

22AV500U 21.6" diagonal 720p HD LCD TV

TOSHIBA
Leading Innovation >>>

22AV500U
720p HD LCD TV



ADVANTAGE

- 720p HD Display
- DynaLight™ Dynamic Backlight Control for Deep Black Levels
- ATSC / QAM Digital Tuner for Over-the-Air and Cable-in-the-Clear Digital Tuning
- 2 HDMI™ Digital Inputs
- PC Input (15 Pin, D-sub)
- High-Gloss Black Cabinet

LEADING THE WAY IN
HOME ENTERTAINMENT
INNOVATION



PRELIMINARY

22AV500U

The 22AV500U features DynaLight™ dynamic backlight control for a deeper HD picture, and a PC Input for use as a computer monitor. Plus, it comes in a high-gloss cabinet that is less than 18" high to fit beneath most standard-size kitchen cabinets. The 22AV500U also includes Native Mode™, Gaming Mode, a second HDMI™ digital input, and ENERGY STAR® compliance.

DynaLight™ Backlight Control utilizes advanced image processing to monitor the brightness of each video frame, and adjust the backlight intensity accordingly. This precision creates seamless transitions with deep blacks for increased detail and depth analysis.

Gaming Mode enhances the gaming experience by reducing the amount of time it takes for the signal to travel from the game controller to the TV.

Cabinet	High-Gloss Black
Screen Size (measured diagonally)	21.6"

LCD PANEL:

Resolution	720p
Dynamic Backlight Control	DynaLight™

VIDEO:

Video Processor	10 Bit
Video Scan Rate	60Hz
Cinema Mode 24fps ¹	3:2 Pull-Down
TheaterWide® Modes	•
Color Temperature Control	•
Native Mode™	•

AUDIO:

Speaker System	Thin-Line
----------------	-----------

CONVENIENCE:

Built-In TV Tuning	NTSC/ATSC/QAM
Auto Aspect Control	•
Sleep Timer	•
Gaming Mode	•
Channel Browser™	•
Channel Labeling	•
Input Labeling	•
ENERGY STAR® Compliant	•

JACK PACK:


HDMI™ Digital Inputs	2
ColorStream® Component Video Inputs	1
Front A/V / Rear A/V / Rear S-Video	0 / 1 / 1
PC Input (15 Pin, D-sub)	1
Analog Audio Out	Fixed
Dolby® Digital Optical Out	•

REMOTE CONTROL:

Type	4 Item Universal ²
------	-------------------------------

PRODUCT & PACKAGING:

Unit Dimensions (WHD) in. (with stand)	21.1 x 16.2 x 8.9
Unit Dimensions (WHD) in. (without stand)	21.1 x 14.6 x 2.9
Carton Dimensions (WHD) in.	23.7 x 20.7 x 6.6
Unit Weight	14.1 lbs
Carton Weight	17.4 lbs
UPC Code	022265001592



¹Viewing 24 frames per second requires content created in 480p / 24 frames/second.

²In some cases, the universal remote may not operate additional devices or certain features of such devices, in which case, it is suggested that you use the original remote control for the applicable device.

<http://www.tacp.toshiba.com> Customer Solutions: 800.631.3811

© Toshiba America Consumer Products, L.L.C.

82 Totowa Road, Wayne, NJ 07470 (2008). All Rights Reserved (8/08.08)

ColorStream and TheaterWide are registered trademarks of Toshiba America Consumer Products, L.L.C. Channel Browser, CineSpeed, DynaLight, and Native Mode are trademarks of Toshiba America Consumer Products, L.L.C. Dolby and the double-D symbol are registered trademarks of Dolby Laboratories. ENERGY STAR is a registered mark owned by the U.S. Government. HDMI, the HDMI logo and High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing LLC. VESA is a registered trademark of Video Electronics Standards Association.